


DuPont™ Cyrel® 3000 P

STATE OF THE ART PROCESSOR

DuPont Packaging Graphics



DuPont™ Cyrel® 3000 P



Technical Drawing

DuPont Packaging Graphics is a leading supplier serving the package printing markets with DuPont™ Cyrel® flexographic solutions. The Cyrel® systems for analogue and digital applications, which are available for solvent and thermal processing, comprise sheet photopolymer plates, continuous sleeves, plate making and mounting equipment. DuPont's complete range of equipment is Advancing Flexography for over 30 years. The DuPont™ Cyrel® systems are renowned for their unmatched production performance, for toping plate quality and abridge the overall pre-press workflow.

The Cyrel® 3000 P is designed with customer needs in mind, it is easy to install, support, maintain and operate. It is robust, extremely cost effective and reliable.

Application

- Maximum plate size 1,320 x 2,250 mm
- Innovative washout concept
- High dot resolution and fine line definition
- Integrated viscosimeter
- Robust and easy to support
- Optimum productivity

Product Features

DuPont™ Cyrel® 3000 P is capable of processing highest quality photopolymer plates up to a nominal format of 1,320 x 2,250 mm (52 inch x 88 inch). The unit is easy to support and maintain, simple to operate, extremely reliable, robust and cheap to run.

High dot resolution, excellent line definition, deep reverses and clean floor are achieved to meet the highest Flexo standard irrespective of whether thick, thin, narrow or large plates are being processed.

An innovative washout concept consisting of 6 flat brushes transverse to each other, and contra-rotating round brushes wash out the non-polymerised parts of the plate. Cleaning takes place through contra-rotating round brushes moistened with fresh solvent, clearing the plate of washout solution.

At the exit section, the plate is pulled over a rotating plush surface and pre-dried. At the same time the relief side can air dry.

The solvent temperature is programmable between 15 °C to 30 °C (59 °F to 86 °F) to handle the different brands of solvents available to the industry. The speed at which the plates pass through can be preset to adapt to the individual plate types. The integration of fresh solvent is controlled via a viscosimeter, which is constantly monitoring the solvent saturation during the entire process. The unit is operated and controlled through a large colour touch screen panel. The computer control board may store up to 21 different wash-out plate programs.



The miracles of science™

Technical Data		
General	Details	Other Notes
Equipment Name	DuPont™ Cyrel® 3000 P	Incremental solvent processor
SAP Article Number	MH74544	
Packing	Crated	
Max. nominal plate width	1,320 mm – 52 inch	
Min. nominal plate width	200 mm – 7.87 inch	
Max. nominal plate length	2,250 mm – 88.5 inch	
Plate thickness	0.5 mm to 7.0 mm	0.019 inch to 0.27 inch
Fresh solvent tank	23 litres – 5.0 GAL – UK	
Min. solvent volume for operation	70 litres – 15.4 GAL – UK	
Max. solvent volume for operation	90 litres – 19.8 GAL – UK	
Max. tank volume	115 litres – 25.3 GAL – UK	
Electrical (field configurable)	380 / 400 Volt – 50 / 60hz* 220 / 230 Volt – 50 / 60hz**	3Ph / N / PE* 3Ph / PE**
Power (nominal)	8 kW	
Current (nominal load)	16 Amp @ 400 Volt* 25 Amp @ 230 Volt**	Connecting wires 5x 2,5 mm ²
Grounding	≤ 0.1 Ω	Ground bar to equipment frame and to electrical supply ground
Exhaust	Ø 100 mm – 3.9 inch	200 m ³ / h – 117.7 scfm (min)
Environmental Data	Temperature range 15°C to 30°C – 59°F to 86°F	Relative humidity From 40% to 60% non-condensing
Compressed Air supply	6 bar minimum	200 l / min – 423.8 ft ³ / hour
Dimension L	4,350 mm – 171.2 inch (un-crated)	4,700 mm – 185.0 inch (crated)
W	1,980 mm – 77.9 inch (un-crated)	2,300 mm – 90.5 inch (crated)
H	1,050 mm – 41.3 inch (un-crated)	1,580 mm – 62.2 inch (crated)
Weight	1,320 kg – 2.910 lbs (un-crated)	1,770 kg – 3.902 lbs (crated)
Colour	DuPont Grey	

All technical information set out herein is provided free of charge and is based on technical data, which DuPont believes to be reliable. It is intended for use by persons having skill, at their own discretion and risk. The handling precaution information contained herein is given with the understanding that those using it will satisfy themselves that their particular conditions of use present no health or safety hazards. Since conditions of product use are outside of our control we make no warranties express or implied in relation thereto and therefore cannot accept any liability in connection with any use of this information. Nothing herein is to be taken as a license to operate under, or a recommendation to infringe any patents.

Du Pont de Nemours (Deutschland) GmbH
 DuPont Imaging Technologies
 Hugenottenallee 173
 63263 Neu-Isenburg
 Deutschland
 Tel: +49 (0) 6102 18 4400

Du Pont (U.K.) Limited
 DuPont Imaging Technologies
 Wedgwood Way, Stevenage
 Hertfordshire SG1 4QN
 United Kingdom
 Tel: +44 (0) 1438 734485

To learn more, visit www.cyrel.co.uk
 or contact your Cyrel® specialist



The miracles of science™

DuPont Packaging Graphics

“Advancing Flexography”